

PURETECH

PVO250X50-Ø25 HL58

EAN 4031582482096



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, black |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 250 mm |
| Tread width | 50 mm |
| Axle hole diameter | 25 mm |
| Hub length | 58 mm |
| Hardness of tread (A) | 85 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ○ ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Puretech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 180 kg |
| Load capacity Static | 360 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 2.038 kg |

PURETECH

PVO250X50-Ø25 HL58

EAN 4031582482096



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

