

NOVATECH

ITP 125x50-Ø20 HL60 cv

EAN 4031582330458



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE


Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	500 kg
Nosivost na 6 km/h	400 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.84 kg

TOCAK

Tread profile	konveksan
Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D




NOVATECH

ITP 125x50-020 H160 cv

EAN 4031582330153

Broj porudžbine 00808844



BETTER MOBILITY. BETTER LIFE.