PRODUCT INFORMATION

LUMINA

AA25PJI050S70-8X15 TFR

EAN 4031582389142



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel caster with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.13 in
Overall width	2.17 in
Overall weight	0.21 lb

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	2.48 in
Swivel interference	4.96 in
Thread diameter	0.31 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.39 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.31 in
Stem length	0.59 in

© Copyright 2026 TENTE International GmbH