

# ALPHA STAINLESS

8470IDC100P30-13 TDK

EAN 4031582382174



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel radius	3.58 in
Swivel interference	7.17 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor
Load capacity at 1.8 mph	176.37 lb
Load capacity at 2.5 mph	176.37 lb
Load capacity at 3.7 mph	176.37 lb
Stainless	✓
Load capacity Static	352.74 lb
Overall height	5.04 in
Overall weight	0 lb

## WHEEL

Body material	Aluminum
Tread material	Damping, heat resistant
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in