

DURATECH

TOP 082X66-Ø20 HL66

EAN 4031582331042
Order number 00827823



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	82 mm
Tread width	66 mm
Axle hole diameter	20 mm
Hub length	66 mm
Body width	66 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	650 kg
Load capacity at 6 km/h	520 kg
Load capacity Static	1300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.462 kg

DURATECH

TOP 082X66-Ø20 HL66

EAN 4031582331042
Order number 00827823



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

