

# MAXTECH EVO

PBO150x38-Ø12 HL34 TFR

EAN 4031582400366



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                          |             |
|--------------------------|-------------|
| Product name             | Maxtech evo |
| Type                     | Wheel       |
| Load capacity at 1.8 mph | 77.16 lb    |
| Electric conductive      | no          |
| Stainless                | no          |
| Load capacity Static     | 154.32 lb   |
| Overall weight           | 0.73 lb     |

## WHEEL

|                    |                                    |
|--------------------|------------------------------------|
| Body material      | Polypropylene                      |
| Tread material     | Polyurethane, biosourced, injected |
| Bearing            | Plain bearing                      |
| Threadguards       | Without threadguard                |
| Diameter           | 5.91 in                            |
| Tread width        | 1.5 in                             |
| Axle hole diameter | 0.47 in                            |
| Hub length         | 1.34 in                            |

# MAXTECH EVO

PBO150x38-Ø12 HL34 TFR

EAN 4031582400366



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

