

# ALPHA

3470PXU160P63

EAN 4031582304848



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	297.62 lb
Load capacity Static	595.25 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	7.87 in
Overall weight	4.5 lb

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, biosourced, injected, electric-conductive
Bearing	Plain bearing with synthetic spacer Tube
Axle	Screwed with nut
Diameter	6.3 in
Tread width	1.57 in
Hardness of tread (A)	85 Shore A

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# ALPHA

3470PXU160P63

EAN 4031582304848



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

