

# ELASTECH

IEP300X60-Ø30 TFR

EAN 4031582428483



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminium
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	300 mm
Tread width	60 mm
Axle hole diameter	30 mm
Hub length	60 mm
Hardness of tread (A)	67 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	3.865 kg

# ELASTECH

IEP300X60-Ø30 TFR

EAN 4031582428483



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

