

PRODUCT INFORMATION

SUPRATECH

PJI050x19-Ø8 AZUL

EAN 4031582457247



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.02 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Axle Hole Diameter	6 mm
Hub Length	21.5 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJI050x19-Ø8 AZUL

EAN 4031582457247



BETTER MOBILITY. BETTER LIFE.

Product Drawings

