

DURATECH

MOP 150x50-Ø30 HL60

EAN 4031582320022



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglični lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	50 mm
dimenzija rupa osovina	30 mm
dužina glavnice	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6306

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	2520 kg
Nosivost na 6 km/h	2100 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	4200 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1.45 kg

DURATECH


MOP 150x50-Ø30 HL60

EAN 4031582320022

Broj porudžbine 00801260
Product Drawings



BETTER MOBILITY. BETTER LIFE.




DURATECH

MOP 150x50-Ø30 HL60

EAN 4031582320022

Broj porudžbine 00804260



BETTER MOBILITY. BETTER LIFE.