

PRODUCT INFORMATION

MAXTECH

PAO050x19,5-Ø6x22,6 + ASBUS

EAN 4031582381221



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.03 kg

WHEEL

Diameter	50 mm
Tread width	19.5 mm
Axle Hole Diameter	6 mm
Hub Length	22.6 mm