

# ALPHA

3478PVR100P62 (6)

EAN 4031582458251



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Housing type                | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 75 kg                         |
| Load capacity Static        | 150 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 128 mm                        |
| Overall weight              | 0.542 kg                      |

## WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Polypropylene       |
| Tread material        | Solid rubber, black |
| Bearing               | Roller bearing      |
| Axle                  | Screwed with nut    |
| Threadguards          | Without threadguard |
| Diameter              | 100 mm              |
| Tread width           | 35 mm               |
| Hardness of tread (A) | 85 Shore A          |

## HOUSING

|               |                    |
|---------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape    | Broad              |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 103 mm            |
| Plate width                 | 85 mm             |
| Plate hole length (Minimum) | 77 mm             |
| Plate hole length (Maximum) | 80 mm             |
| Plate hole width (Maximum)  | 60 mm             |
| Plate hole diameter         | 9 mm              |

# ALPHA

3478PVR100P62 (6)

EAN 4031582458251



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

