

INTEGRAL TWIN TORSION

3940UAC125R05-32 RAL7001

EAN 4031582382532



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Integral twin torsion
Tip kućišta	Okretanje Tocak
Standard	Slično EN12531 - Bolnički kreveti
Nosivost na 3 km/h	125 kg
Nosivost na 4 km/h	125 kg
Statički Nosivost	250 kg
Temperaturni opseg (Minimalno)	-30 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	150 mm
Ukupna širina	62 mm

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj, nerdjajuci
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	12 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	40 Šor D

KUCISTE

Materijal	Čelični list, težak
oblik viljusa	kuciste za dva Tocak
okretni lezaj	precizini kuglicni lezaj
ofset	37,5 mm
okretni radijus	100 mm
Otpor okretanju	200 mm

PRILAGOĐAVANJE

Tip uklapanja	stablo, okrugla
Prečnik sraf	32 mm
Dužina sraf	45 mm

INTEGRAL TWIN TORSION

3940UAC125R05-32 RAL7001

EAN 4031582382532



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

