

DURATECH

TOP 065x32-Ø12 HL32

EAN 4031582332315



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	65 mm
Tread width	32 mm
Axle Hole Diameter	12 mm
Hub Length	32 mm
Body width	32 mm
Hardness of tread (D)	75 Shore D
Bearing type	6201

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	290 kg
Load capacity at 6 km/h	240 kg
Electric Conductive	No
Stainless	No
Load capacity Static	480 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.17 kg

DURATECH

TOP 065x32-Ø12 HL32


EAN 4031582332315

Order number 00829018

Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

DURATECH

TOP 065x32-Ø12-HL32

EAN 4031582382315

Order number 00829018



BETTER MOBILITY. BETTER LIFE.