

NOVATECH

ETX085X85-Ø20 HL95-F

EAN 4031582369649



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	3.35 in
Tread width	3.35 in
Axle hole diameter	0.79 in
Hub length	3.74 in
Hardness of tread (A)	92 Shore A
Sealing type	F
Suitable for	jungheinrich

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	1763.7 lb
Load capacity Static	3527.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F

TECHNICAL DRAWINGS

