

# AGILA

2477YGO125R47-32-35

EAN 4031582341805



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 100 kg                        |
| Electric conductive         | ✓                             |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 40 °C                         |
| Overall height              | 163 mm                        |

## WHEEL

|                       |                                           |
|-----------------------|-------------------------------------------|
| Body material         | Polypropylene, electric conductive        |
| Tread material        | Thermoplastic rubber, electric-conductive |
| Bearing               | Plain bearing                             |
| Threadguards          | Without threadguard                       |
| Diameter              | 125 mm                                    |
| Tread width           | 32 mm                                     |
| Hardness of tread (A) | 87 Shore A                                |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 41 mm               |
| Swivel radius       | 131 mm              |
| Swivel interference | 262 mm              |

## FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, square                                 |
| Expander fitting (Minimum) | 32 mm                                                      |
| Expander fitting (Maximum) | 35 mm                                                      |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

# AGILA

2477YGO125R47-32-35

EAN 4031582341805



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

