

# AGILA

2477UAP125R07-Ø31-35

EAN 4031582327199



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Type                        | Swivel caster with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 220.46 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | 14 °F                         |
| Temperature range (Maximum) | 104 °F                        |
| Overall height              | 6.42 in                       |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 1.61 in             |
| Swivel radius       | 5.16 in             |
| Swivel interference | 10.31 in            |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 4.92 in                |
| Tread width           | 1.26 in                |
| Hardness of tread (D) | 40 Shore D             |

## FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, round                                  |
| Expander fitting (Minimum) | 1.22 in                                                    |
| Expander fitting (Maximum) | 1.38 in                                                    |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

# AGILA

2477UAP125R07-Ø31-35

EAN 4031582327199



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

