

# NOVATECH

ITP200X50-Ø20 HL60 SUPER CONVEX R25

EAN 4031582444674



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Aluminium              |
| Tread profile         | convex                 |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | Without threadguard    |
| Diameter              | 200 mm                 |
| Tread width           | 50 mm                  |
| Axle hole diameter    | 20 mm                  |
| Hub length            | 60 mm                  |
| Hardness of tread (A) | 92 Shore A             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Novatech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 700 kg                        |
| Load capacity Static        | 1400 kg                       |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 1.457 kg                      |

# NOVATECH

ITP200X50-Ø20 HL60 SUPER CONVEX R25

EAN 4031582444674



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

