

S70-10X25 / 11 DRILLED STEM

EAN 4031582411911



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Overall height	0.24 in
Overall weight	0.11 lb

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.98 in