

STEM

S70-10X25 / 11 DRILLED STEM

EAN 4031582411911



Image may differ from the original product

PERFORMANCE

Corrosion resistance



CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Overall height	0.24 in
Overall weight	0.11 lb

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.39 in
Stem length	0.98 in