

NOVATECH

ETP 085X90-Ø20 HL90

EAN 4031582383843
Order number 00828567



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Steel, iron |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 85 mm |
| Tread width | 90 mm |
| Axle hole diameter | 20 mm |
| Hub length | 90 mm |
| Body width | 90 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |
| Bearing type | 6204 |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Novatech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 800 kg |
| Load capacity at 6 km/h | 640 kg |
| Load capacity Static | 1600 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 1.36 kg |

TECHNICAL DRAWINGS

