

LEVINA

5370PIP150R05-22X45

EAN 4031582363333



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Levina |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 176.37 lb |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 7.48 in |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| | soft |
| Tread material | Solid rubber, non-marking |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 5.91 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 75 Shore A |

HOUSING

| | |
|---------------------|----------------|
| Material | Polyamide |
| Fork shape | Slim |
| Swivel bearing | Two ball races |
| Offset | 1.5 in |
| Swivel radius | 4.45 in |
| Swivel interference | 8.9 in |

FITTING

| | |
|---------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 0.87 in |
| Bolt length | 1.77 in |



Universal Design Award



Deutscher Designer Club

PRODUCT INFORMATION

LEVINA

5370PIP150R05-22X45

EAN 4031582363333



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Universal
Design
Award



Deutscher
Designer
Club