

GLIDE

A229Y0I050B10-11X20/10 9011/1016

EAN 4031582319613



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Glide
Type	Customized solution
Electric conductive	Yes
Stainless	no
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	1.3 in
Overall width	1.97 in
Overall weight	0.14 lb

HOUSING

Housing Material	Polypropylene
Fork shape	Straight
Swivel bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Dome diameter	1.5 in
Collar diameter	1.97 in

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	1.97 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in
Stem length	0.79 in

GLIDE

A229YOI050B10-11X20/10 9011/1016

EAN 4031582319613

Order number 00075112

Product Drawings



BETTER MOBILITY. BETTER LIFE.

