

# NOVATECH

RK.ETP085X75-Ø47X15

EAN 4031582330809



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	3.35 in
Tread width	2.95 in
Hardness of tread (A)	92 Shore A
Ball bearing diameter	1.85 in
Ball bearing width	0.59 in

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	1543.23 lb
Load capacity Static	3086.47 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F

## TECHNICAL DRAWINGS

