

KAPPA LOAD

9650MOP200P64 TFR

EAN 4031582481860



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Swivel castor
Load capacity at 1.8 mph	4409.24 lb
Load capacity at 2.5 mph	4409.24 lb
Load capacity at 3.7 mph	4409.24 lb
Load capacity Static	8818.48 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	10.04 in
Overall weight	22.18 lb

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	3.15 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	2.6 in
Swivel radius	6.54 in
Swivel interference	13.07 in

FITTING

Fitting type	Rectangular plate
Plate length	6.89 in
Plate width	5.51 in
Plate hole length (Maximum)	5.51 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.59 in

KAPPA LOAD

9650MOP200P64 TFR

EAN 4031582481860



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

