

PRODUCT INFORMATION

ELASTECH

UER200x46-Ø20 HL58

EAN 4031582442892



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 881.85 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 1763.7 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 176 °F                        |
| Overall weight              | 2.45 lb                       |

WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Tread hardness        | soft                            |
| Body material         | Polyamide                       |
| Tread material        | Elastic tire, black, vulcanized |
| Bearing               | Roller bearing                  |
| Threadguards          | Without threadguard             |
| Diameter              | 7.87 in                         |
| Tread width           | 1.81 in                         |
| Axle hole diameter    | 0.79 in                         |
| Hub length            | 2.28 in                         |
| Hardness of tread (A) | 64 Shore A                      |

