

ALPHA STAINLESS

8478IDC100P62

EAN 4031582347081



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall height	128 mm
Overall weight	0.671 kg

WHEEL

Body material	Aluminium
Tread material	Damping, heat resistant
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Hardness of tread (A)	75 Shore A

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Stainless	✓

FITTING

Fitting type	Rectangular plate
Plate length	100 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Maximum)	60 mm
Plate hole diameter	9 mm

ALPHA STAINLESS

8478IDC100P62

EAN 4031582347081



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

