

ELASTECH

UER200X46-Ø20 HL58

EAN 4031582442892



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	46 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (A)	64 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	1.11 kg

ELASTECH

UER200X46-Ø20 HL58

EAN 4031582442892



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

