PRODUCT INFORMATION

DURATECH SILENT

UOT 100x36-Ø8,4 HL45

EAN 4031582338041

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing, damped
Wheel Color	Natural white
Diameter	100 mm
Tread width	36 mm
Axle Hole Diameter	8.4 mm
Hub Length	45 mm
Body width	36 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech silent
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall weight	0.3 kg

© Copyright 2026 TENTE International GmbH


DURATECH SILENT

UOT 100x36-Ø8,4 HL45

EAN 4031582338041

Order number 00033627

Product Drawings



© Copyright 2026 TENTE International GmbH