

PURETECH

PVO100X35-Ø12 HL44,4

EAN 4031582442342



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll performance	● ● ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.195 kg

PURETECH

PVO100X35-Ø12 HL44,4

EAN 4031582442342



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

