

MAXTECH

UAR 125X38-Ø12

EAN 4031582323160
Order number 00030960



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing
Wheel color	Blue gray (RAL7031)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.5 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.5 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	0.7 lb

MAXTECH

UAR 125X38-Ø12

EAN 4031582323160
Order number 00030960



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

