

DURATECH

UOP100X36-Ø8 HL45

EAN 4031582442809



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	36 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.25 kg

DURATECH

UOP100X36-Ø8 HL45

EAN 4031582442809



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

