PRODUCT INFORMATION

# AGILA

## 2477UAP100R05-28 M8/19

EAN 4031582302233



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Agila |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall Height | 138 mm |
| Overall width | 60 mm |
| Overall weight | 1.06 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 43.5 mm |
| Swivel radius | 131 mm |
| Swivel interference | 262 mm |
| Dome diameter | 60 mm |

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel Color | Silver grey (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

### FITTING

| | |
|---|---|
| Fitting type | Solid stem, round |
| Bolt diameter | 28 mm |
| Bolt length | 45 mm |
| Bolt thread position | 19 mm |
| Bolt mounting holes quantity | 2 |

© Copyright 2026 TENTE International GmbH


# AGILA


## 2477UAP100R05-28 M8/19

EAN 4031582302233

Order number 00030016

**Product Drawings**



© Copyright 2026 TENTE International GmbH