

MAXTECH

PNP300X42-Ø12 HL45

EAN 4031582411089



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	300 mm
Tread width	42 mm
Axle hole diameter	12 mm
Hub length	45 mm
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

MAXTECH

PNP300X42-Ø12 HL45

EAN 4031582411089



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

