

DURATECH

TOP 080X70-Ø20 HL76

EAN 4031582322576

Broj porudžbine 00804172



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	70 mm
dimenzija rupa osovina	20 mm
dužina glavcine	76 mm
Širina tela	70 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204ZV

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	560 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,446 kg

DURATECH

TOP 080X70-Ø20 HL76

EAN 4031582322576

Broj porudžbine 00804172



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

