

# ALPHA

3480PQR260P65 BLACK/DARKBLUE

EAN 4031582438239



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Type	Swivel castor
Load capacity at 3 km/h	150 kg
Load capacity Static	300 kg
Overall height	310 mm
Overall weight	5 kg

## WHEEL

Body material	Polypropylene
Tread material	Pneumatic tyre, block profile
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	260 mm
Tread width	85 mm

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races, reinforced or stainless
Offset	90 mm
Swivel radius	220 mm
Swivel interference	440 mm

## FITTING

Fitting type	Medium rectangular heavy-duty plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	160 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	14 mm

PRODUCT INFORMATION

# ALPHA

3480PQR260P65 BLACK/DARKBLUE

EAN 4031582438239



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

