PRODUCT INFORMATION

ELASTECH

UEP 200x46-Ø20

EAN 4031582328608



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.81 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.81 in
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	881.85 lb
Electric conductive	no
Stainless	no
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	2.74 lb

© Copyright 2026 TENTE International GmbH


ELASTECH

UEP 200x46-Ø20

EAN 4031582328608

Order number 00023479

Product Drawings



© Copyright 2026 TENTE International GmbH