

LUMINA

AA20POI050P41-38X38 TFR

EAN 4031582385595



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Lumina |
| Type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 88.18 lb |
| Load capacity Static | 176.37 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 2.48 in |
| Overall width | 2.17 in |
| Overall weight | 0.25 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 1.97 in |
| Tread width | 0.31 in |
| Hardness of tread (D) | 65 Shore D |

HOUSING

| | |
|---------------------|----------------------------|
| Material | Polypropylene |
| Fork shape | Twin wheel housing, closed |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 1.93 in |
| Swivel interference | 3.86 in |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 1.5 in |
| Plate width | 1.5 in |
| Plate hole length (Maximum) | 1.1 in |
| Plate hole width (Maximum) | 1.1 in |
| Plate hole diameter | 0.17 in |