

# SUPRATECH

PJP125X40-Ø8,3 HL45

EAN 4031582444186



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (A)	65 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	180 kg
Load capacity Static	360 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.24 kg

# SUPRATECH

PJP125X40-Ø8,3 HL45

EAN 4031582444186



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

