

AGILA TWIN

2977PIO075P30-10

EAN 4031582362305



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	99 mm
Overall weight	0.586 kg

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	31.4 mm
Swivel radius	99 mm
Swivel interference	198 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

AGILA TWIN

2977PIO075P30-10

EAN 4031582362305



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

