

# GLIDE

A229POI050B10-11X20

EAN 4031582319606  
Order number 00072176



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Glide
Housing type	Customized solution
Load capacity at 1.8 mph	66.14 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	1.3 in
Overall width	1.97 in
Overall weight	0.12 lb

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	1.97 in
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Polypropylene
Fork shape	Straight
Swivel bearing	Stem, swiveling
Dome diameter	1.5 in
Collar diameter	1.97 in

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

PRODUCT INFORMATION

# GLIDE

A229POI050B10-11X20

EAN 4031582319606  
Order number 00072176



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

