PRODUCT INFORMATION

DURATECH HEAT

WOG 075x25 HL31,8 black

EAN 4031582382891

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Black
Diameter	2.95 in
Tread width	0.98 in
Axle hole diameter	0.31 in
Hub length	1.25 in
Body width	0.98 in
Hardness of tread (D)	80 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	110.23 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	220.46 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	273.2 °F
Overall weight	0.19 lb

© Copyright 2026 TENTE International GmbH


DURATECH HEAT

WOG 075x25 HL31,8 black

EAN 4031582382891

Order number 00039564

Product Drawings



© Copyright 2026 TENTE International GmbH