

ALPHA

3488PQR260P65 BLACK/DARKBLUE

EAN 4031582438246



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Load capacity at 1.8 mph	330.69 lb
Load capacity Static	661.39 lb
Overall height	12.2 in
Overall weight	7.72 lb

WHEEL

Body material	Polypropylene
Tread material	Pneumatic tire, block profile
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	10.24 in
Tread width	3.35 in

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Rectangular plate
Plate length	7.87 in
Plate width	6.3 in
Plate hole length (Maximum)	6.3 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.55 in