

# FOOTMASTER

## FOOT MASTER GATD-125-ASF-HUD

EAN 4031582496598  
Order number 00800210



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

### PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

### CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	440 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall height	175 mm
Overall width	141 mm
Overall weight	11.154 kg

### WHEEL

Bearing	Unmachined hub
Diameter	125 mm
Tread width	35 mm
Body width	35 mm

### HOUSING

Offset	33 mm
Swivel radius	107 mm
Swivel interference	214 mm
Dome diameter	130 mm

### FITTING

Plate length	145 mm
Plate width	145 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	11 mm

# FOOTMASTER

FOOT MASTER GATD-125-ASF-HUD

EAN 4031582496598  
Order number 00800210



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

