

ALPHA

3488PNR260P65 YELLOW/DARKBLUE

EAN 4031582438222



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Overall height	310 mm
Overall weight	3.5 kg

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	260 mm
Tread width	85 mm

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Rectangular plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	160 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	14 mm