PRODUCT INFORMATION

ELASTECH

IEP 200x50-Ø25 HL60

EAN 4031582319743

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel Color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Axle Hole Diameter	25 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	●●○○○
Movement Noise	●●●●●
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	450 kg
Load capacity at 6 km/h	360 kg
Electric Conductive	No
Stainless	No
Load capacity Static	900 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	1.71 kg

© Copyright 2026 TENTE International GmbH


ELASTECH

IEP 200x50-Ø25 HL60

EAN 4031582319743

Order number 00804060

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

IEP 200x50-Ø25 HL60

EAN 4031582319743

Order number 00307040



© Copyright 2026 TENTE International GmbH