

DURATECH

MOP 250X80-Ø50 HL90

EAN 4031582320084

Broj porudžbine 00830850



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	80 mm
dimenzija rupa osovina	50 mm
dužina glavcine	90 mm
Širina tela	80 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6310

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	6600 kg
Nosivost na 6 km/h	5500 kg
Statički Nosivost	11000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	6,202 kg

DURATECH

MOP 250X80-Ø50 HL90

EAN 4031582320084

Broj porudžbine 00830850



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

