

# ALPHA

3478IEP200P63 TFR

EAN 4031582388442



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	240 mm

## WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (A)	67 Shore A

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

## FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ALPHA

3478IEP200P63 TFR

EAN 4031582388442



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

