

# AGILA

2470PJO125R07-Ø21,5-24

EAN 4031582324969



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Type                        | Swivel caster             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 220.46 lb                 |
| Electric conductive         | no                        |
| Stainless                   | no                        |
| Load capacity Static        | 440.92 lb                 |
| Temperature range (Minimum) | 14 °F                     |
| Temperature range (Maximum) | 104 °F                    |
| Overall height              | 6.42 in                   |
| Overall weight              | 1.69 lb                   |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 1.61 in             |
| Swivel radius       | 4.07 in             |
| Swivel interference | 8.15 in             |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | Without threadguard  |
| Diameter              | 4.92 in              |
| Tread width           | 1.26 in              |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, round                                  |
| Expander fitting (Minimum) | 0.85 in                                                    |
| Expander fitting (Maximum) | 0.94 in                                                    |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

# AGILA

2470PJO125R07-Ø21,5-24

EAN 4031582324969



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

