

ALPHA

3478UOH125P62

EAN 4031582307030
Order number 00026168



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	275 kg
Load capacity Static	550 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	155 mm
Overall width	85 mm
Overall weight	0.693 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Colour	Blue passivated

FITTING

Fitting type	Rectangular plate
Plate length	103 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	9 mm

ALPHA

3478UOH125P62

EAN 4031582307030
Order number 00026168



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

